


Hydrocarbons from water DIN EN ISO 9377-2 (DEV H53)**Column:** Zebtron™ ZB-1HT, GC Cap. Column 15 m x 0.32 mm x 0.25 µm, Ea**Phase:** 100% Dimethylpolysiloxane**Dimensions:** 15 meters x 0.32 mm x 0.25 µm**Order No:** 7EM-G014-11**Oven Profile:** 50 °C for 2 min to 320 °C @ 30°C/min for 5 min**Carrier Gas:** Constant Flow Helium, 2 mL/min**Injection:** Splitless :1 20 µL @ 300°C**Detection:** Flame Ionization (FID) (330°C)**Analyst Note:** Large volume injection used.
Courtesy of Dr. Alexander Ruderisch, Agrolab Labor GmbH, Bruckberg**Products used in this application:**

18153

**ANALYTES:**

- 1 Decane
- 2 Tetracontane

